



In-line Filtration

Advantages

- Long filter endourance
 Up to now over 3 years
- Low Maintenance
 No continuous maintenance necessary
- Low running costs
 No tube changes, no chemicals
- Easy cleaning
 Normally every 2 to 6 weeks
 Raise it, wipe it, reinsert it!
 It takes only 1 minute
- Weight4 kg Easy to handle



Technical Data

- Low-maintenance filter 350 x 450 mm
- Filtrate flow: max. 1000 ml/h adjustable
- Ready mounted on a steel mounting place (1.4571)
- Distance from analyzer: max. 100 m
- · Control unit ready mounted in a glass-fibre cabinet
- Membrane pump, manometer, SPS and terminal box included
- Special filters for UV and chemical resistance
- Heated sample line with thermostat
- Power supply230 V / 50 Hz, 20 W

More than 3 years of practical experience with the easiest and lightest filtration.





SPX Flow Technology Norderstedt GmbH - Werkstraße 4 - D-22844 Norderstedt Phone: +49 40 52202-0 Fax: +49 40 52202-444 E-Mail: branluebbe@spx.com

SPX reserves the right to incorporate our latest design and material changes without notice or obligations.

Design features, materials of construction and dimensional data, as described in this bulletin, are provided for your information only and should not be relied upon unless confirmed in writing. Please contact your local sales representative for product availability in your region. For more information visit www.spx.com.