SITRANS F M MAGFLO Electromagnetic Flowmeters Explore the Siemens Solution

SI

MAGFLO





SIEMENS

What makes MAGFLO simply better?

MAGFLO flowmeters will help you do an easier job of managing flow. Whether it is installation, managing operations or verifying continuous accuracy, customers rely on MAGFLO to improve the entire value chain of activities.

Greater flexibility

- Wide product program
- Compact or remote installation using the same transmitter and sensor
- USM II communication platform for easy integration with all systems

Easier to commission

- SENSORPROM enables instant measurement from the start of power-up
- User settings automatically stored in the SENSORPROM

Easier to operate & maintain

- No moving parts
- Robust construction and materials
- Uniform user interface for all MAGFLO products

Easier to service

• Transmitter replacement requires no programming. SENSORPROM automatically updates all settings after initialization.

Room for growth

- Plug & Play communication modules are available in a wide range of bus-protocols
- Add-on communication modules allow future upgrades without investing in a new flowmeter.

Diagnostics: Application and metering

- Identification in clear text and Error-log
- Error categories: function; warning; permanent and fatal
- Transmitter self check including outputs and accuracy
- Sensor check
- Overflow
- Empty pipe; partical filling; low conductivity; electrode fouling
- System verification with MAGFLO Verificator











The dedicated MAGFLO program

Siemens offers a comprehensive selection of flowmeter technologies.

Choosing the right flowmeter for the right application can dramatically improve your operations...and improve your bottom line. Get industry-specific solutions for:

- Water & Wastewater
- Chemical
- Food & Beverage
- Pharmaceutical
- Mining/Aggregates/Cement
- Pulp & paper
 Power & Utilities

Siemens can provide the best electromagnetic flowmeter options available. With Siemens flowmeters you get:

- The best value for the money
- The highest quality and most advanced technology
- User-friendly products and services
- Superior worldwide service and support









Touchpad Touch response keypad with LED light feedback for safe & easy operation.



SENSORPROM The memory unit will store calibration, programming and setup data.



Communication Modules

The USM II makes flowmeter networking installation and configuration easy. It is compatible with virtually every communication standard.



MAGFLO Verificator In-situ verification to ensure continuous accuracy and confident flow measuring.

One Platform. Infinite Solutions

Thanks to Siemens philosophy of modular design, we are making it easy to buy the magnetic flowmeter solutions and services you need.





MAG 5000

MAG 6000/Ex

safetv barrier

IP66 / NEMA 4





MAG 5000/

6000 19"

Panel mount

IP20 / NEMA 2



MAG 6000 I

MAG 6000 I

(Ex d)

MAG 6000

Wallmount Junction Box



MAG 6000 Electrode cleanina IP66 / NEMA 4





Modular pulsed DC magnetic flowmeters

You can combine all the basic components of our flowmeters - the transmitters, sensors and more – because they are engineered on the shared Siemens technology platform.

One of a kind technologies

Siemens offers industry specific and proprietary solutions:



TRANSMAG 2 The patented **pulsed AC** magnetic flowmeter The ideal solution for mining, cement, and pulp & paper.



MAG 8000 Battery-powered magnetic water meters for distribution, revenue and irriga-

tion.



Control room

Gain full performance in the Value Chain

Totally Integrated Automation Solutions – only from Siemens

With its Totally Integrated Automation (TIA) strategy, Siemens is in a class of its own as the sole provider of a common solutions platform for all industries. Designed for the individual customer demands, TIA enables the realization of industry specific automation solutions that significantly increase production while also offering sound investment security. These solutions are designed to ideally support companies in optimizing their plant, system and process flows.

Best of all, Siemens TIA solutions are completely scalable.

You can start with a stand-alone installation today, secure in the knowledge that you can always integrate your system tomorrow.

- · Confirm flowmeters are operating optimally and are properly utilized
- Reduce downtime through predictive maintenance programs
- · Access real-time flow data • Generate the highest yield by
- driving down waste and costs • SIMATIC PDM software tool for the operation, configuration, parameterization, maintenance and diagnosis of intelligent field instruments based on the worldwide leading EDD standard.

with TIA

Control level/Field level Combine and integrate HARTAAA

4

The Transmitter Program What's right for you?





MAG 5000 and MAG 6000 For high performance, easy operation and reduced maintenance.

MAG 5000 is the truly robust solution for all-around applications. MAG 6000 is for the more demanding applications where higher accuracy and greater functionality is required.

MAG 6000 Industry

This transmitter is designed for the special demands in the process industry. The robust, full-metal housing provides superb protection, even in the harshest industrial environments. Full input and output functionality is given even in the ATEX EEx d version.

Guaranteed Performance

- Compact or Remote InstallationSuperior signal resolution for
- optimized turn-down ratioDigital Signal Processing with
- unlimited possibilities • User configurable operation
- User configurable operation menu with password protection

- Multiple functional output for process control
- Self-diagnostics for error detection and logging
- Batch control
- Multi-lingual display and keypad
- Custody Transfer Approved
- Electrode cleaning accessory option

SENSORPROM

Each flow meter has its own identity stored in the SENSORPROM.

The information consists of:

- Calibration data
- "Fingerprint" magnetism properties
- User setup and programming data

The individual calibration and fingerprint data are pre-programmed at the factory, whereas the setup data are customer-specific. This unique combination ensures a cost effective, easy and error-free installation.



"Plug & Play" Communication Modules

USM II (Universal Signal Module) is "Plug & Play" at its very best. It makes flowmeter networking installation and configuration easy.

And it is compatible with virtually every communication standard used today, including PROFIBUS PA/DP, HART, Modbus RTU, DeviceNet and CANopen.

Transmitter	MAG 5000	MAG 6000	MAG 6000 I	MAG 6000 I (Ex d)	
Enclosure	IP67 / NEMA 4X or IP20/	66 / NEMA 2/4 Polyamid	IP67 / NEMA 6 di	e-cast aluminium	
Max measuring Error	0.50 % of rate		0.25 % of rate		
Display		3 line alpha numerio	c LCD with back light		
Inputs & outputs	1 digital input	, 1 current output, 1 pulse/fr	equency output, 1 relay outp	ut	
Communication	HART	HART; Profibus PA/DP; Modb	us RTU; DeviceNet; CANopen	HART; Profibus PA	
Batch function	No	Yes	Yes	Yes	
Power Supply	12 – 24 V AC/DC (or 115 – 230 V AC	18 – 90 DC or 115-230 AC	24 V DC or 115 – 230 V AC	
Approvals	CE; ULc; C-Tick			ATEX EEx d e [ia] ia IIB T6	
		FM Class 1, Div 2		FM Class 1, Div 2	
Custody Transfer Approval	Cold Water	Cold Water, Hot Water, Other Liquids			

The Sensor Program Sensible. Flexible. Reliable

MAG 1100

The flangeless wafer design that meets all flange standards. The MAG 1100 is used in all industries where the corrosion-resistant stainless steel housing and the highly resistant liner and electrodes fit even the most extreme process media.

MAG 1100 FOOD

Especially designed for the food & beverage industry, it offers unique and flexible process connections. It was the first to pass the EHEDG hygienic test and meets all sanitary standards. Its performance is unaffected by suspended solids, viscosity and temperature challenges.

MAG 5100 WATER

A sensor for all water and wastewater applications. With its coned design, increased low-flow accuracy is achieved, making it especially useful for leak detection. It can be made suitable for direct burial and constant flooding. MAG 5100 W complies with drinking water and custody transfer approvals.

MAG 3100

This flexible and comprehensive sensor program offers a wide range of sizes. Liners and measuring electrodes capable of withstanding the most extreme processes are available. Fully welded construction provides a ruggedness that suits the toughest environments.



The coils in the sensor generate a consistent magnetic field. The liquid flowing through the sensor induces a voltage proportional to the flow velocity.









Sensor	MAG 1100	MAG 1100 F	MAG 3100	MAG 5100 W
Size DN	2 – 100** mm / 1/12" to 4"	10 –100 mm / ³/8" to 4"	15 – 2000 mm / ³/8" to 78"	25 – 1200 mm / 1" to 48"
Process temperature	-20 – 200 °C / -5 – 400 °F	-30 – 150 °C / -20 – 300 °F	-40 – 180 °C / -40 – 350 °F	-5 – 70 °C / 23 – 160 °F
Pressure rating max.	PN 40 / M	ax 600 PSI	PN 100 / Max 1500 PSI*	PN 16 / ANSI / AWWA 150
Liner Material		amic FA	Neoprene, EPDM, Ebonite, LINATEX, PTFE, NOVOLAK	Hard Rubber/ Composite elastomer
Electrode Material		num Iloy C	AISI 316 Ti, Hastelloy C, Titanium, Tantalum, Platinum	AISI 316 Ti
Approvals	3A & EHEDG		Custody Transfer	Custody Transfer Drinking Water
	ATEX EEx [ia] [ib] IIB T4-T6		ATEX EEx [ia] [ib] IIB T4-T6 ATEX EEx e [ia] IIC T3 - T6	
		FM Class	5 1, Div 2	

* Optional high-pressure versions available – ** DN 2 and 3 available from 2005



Water Supply and Metering MAG 8000 for applications everywhere

MAG 8000 6 years of non-stop battery driven performance – no mainpower required

MAG 8000 is an affordable batterydriven solution that gives you the flexibility to install a reliable water meter virtually anywhere without sacrificing accuracy or performance. No main power is required.

Battery pack available as an integrated or external battery pack with an IP68 / NEMA 6 enclosure and connection. Graphical display and keypad for simple operation and instant access to information.



Low-flow Detection

The MAG 8000 is a low-flow detection Sensor. Its coned flow tube design greatly improves low-flow performance with minimal pressure drop.





MAG 8000 complies with the OIML R49 water meter standard and is specially engineered for water applications:

- Abstraction
- Distribution/network
- Revenue
- Irrigation

Outstanding performance

MAG 8000 delivers best-in-class performance to optimise water supply. It is optimised for leakage detection and for correct, accurate billing. It is easy to install. And it is low maintenance, delivering long term performance with minimal cost of ownership.

- Flexible power supply
- IP68 / NEMA 6P burial enclosure
- Minimized installation requirements
- Advanced software features
- Integrated data logger
- IrDA for onsite download
- Open communication platform
- Drinking water approvals
- Complies with most international approvals

Intelligent, battery-driven operation

With a combination of high efficiency technology and advanced power management, MAG 8000 can be trusted to deliver long lasting, dependable operation for 6-10 years in a typical revenue application.

MAG 8000		
Sensor Size	DN 50-300 mm / 2"-12" with hard rubber elastomer	
Enclosure	IP68 / NEMA 6P	
Display	Graphical display with touch keypad	
Output	2 individual pulse outputs (include net flow volume)	
Communication	Integrated standard IrDA interface	
Power Supply	Internal or external battery pack	
Features	Data logger with selectable log interval up to 26 months	
	Power management with selectable battery alarm level	
	Real time clock and date	
	Self check feature and automated data back up	
	3 totalizers including one with user reset	

8

Water and Wastewater MAGFLO for water processes

Cost effective solution

The MAG 5000 transmitter and MAG 5100 W sensor are the perfect match for a cost effective solution.

- One solution for all your water & wastewater applications
- No moving parts ensures long term performance
- Hard rubber elastomer liner guarantees consistent accuracy
- Highly resistant to a wide range of chemicals used in treatment plants
- Increased low-flow measurement for leak detection
- Sensor suitable for burial and constant flooding
- Drinking water approvals
- Complies with most international standards and agency approvals
- Built-in ground electrodes eliminate grounding rings

Process optimisation

MAG 6000 with the USM II add-on communication platform makes it easy to integrate MAGFLO information into process applications.

Realize the full benefits of automation

- Optimise management and process control
- Ensure correct dosing and product quality
- Minimise process time and consumption of high-cost chemicals



The Siemens product range provides sensors from 2 mm up to 2000 mm and from 1/12" up to 78"



In-situ MAGFLO Verification Your guarantee for continuous accurate measurement

- Correct revenue metering
- Confidence in process and product quality
- As hand-over of new installations to ensure correct installation
- ISO 9000 and ISO 14001



Hazardous areas

MAG 6000 I (Ex d)

available for use in

hazardous areas.

MAG 6000 I (Ex d)



Chemical dosing

sing the treatment

process.

MAG 1100 for optimi-

MAG 1100



Electrode Cleaning

Automatic self-cleaning

of extreme deposits on

the sensor electrodes.

MAG 6000 electrode cleanings







Chemical Industry The power of protection

Siemens offers the market's most versatile flowmeter program dedicated to work in the harshest environments.

Every component Siemens makes combines the highest levels of safety, quality and reliability with a low cost of ownership.

Highest level of safety and quality

Siemens offers a full range of ATEX and FM approved flowmeters for remote or compact installations.

- Intrinsically safe rated input and outputs
- Compliance with NAMUR NE 21 • Multi-informational, multi-lingual display
- Actual flow & totalizers: forward, reverse & net totals
- Sophisticated self diagnostics
- Error log & error-pending indication



Touchpad

This innovative capacitive touch-sensitive keypad has an LED light indication for positive feedback, ensuring safe and easy operation in hazardous areas without having to open the enclosure.



The MAG 1100 ceramic liner is resistant to virtually all media and combined with the platinum electrodes no application is too tough.



MAG 6000 I (Ex d)



MAG 5000/6000







MAG 1100 with pipe threads



Proven to meet the harsh demands in the chemical industry

Siemens flowmeters have a robust design that meets the demanding applications that flowmeters in the process industry require. They are chemically resistant, fully operational in hazardous environments, and able to perform a number of difficult measurement tasks.

In addition, Siemens offers the in-situ verification for documenting continuous accuracy for crucial process applications, important where verification is required to meet ISO 9001, ISO 14001 or other quality control management programs.



"Plug & Play"



NOVOLAK



SENSORPROM

Communication

With the USM II, Siemens brings flexibility and "future-proof" design one step further with fieldbus modules like Profibus PA/DP, HART, Modbus RTU, DeviceNet and CANopen.

Lifetime corrosive resistance

The often harsh environment in the chemical industry require the use of a wide range of corrosive resistant materials. Siemens offers liner, electrode and housing materials that withstand such extreme process media.

Well fitted liner materials:

PTFE, PFA, Ceramic, NOVOLAK

Electrode materials

AISI 316 Ti, Hastelloy C, Titanium, Tantalum, Platin

NOVOLAK. The revolution in liner materials

Only Siemens offers NOVOLAK, a revolutionary liner material with a smooth, hard and non porous finish that provides the highest level of protection against corrosion, abrasion, high pressure & temperatures, and vacuum conditions. It has the chemical resistance you'd expect from PTFE, with the mechanical strength and stability of steel.

SENSORPROM

It not only stores calibration data but also the programming and setup data entered during commissioning. Ensures fast, easy and reliable servicing.



The confidence of In-situ verification

Unique verification concept based on years of know-how is ideal for quality control management

- In-situ verification requires no interruption of flow or opening of pipes
- Full installation test of transmitter, sensor and cabling
- Testing is made on location without disconnecting any cabling.
- A fully automated verification test in less than 15 minutes





Pharmaceutical Industry For accuracy, sterility and complete confidence

With cost-effective solutions that meet the high standards of accuracy and hygienic design, Siemens provides flow solutions to customers in the pharmaceutical industry which reduce the cost of high purity flow measurements.

MAG 1100

The MAG 1100 is ideally suited for pharmaceutical applications. Its obstruction-free performance minimizes the risk of deposits, and it is unaffected by the suspended solids, viscosity, and temperatures typically found in pharmaceutical processes.

Additional benefits include:

- Suitable for CIP and SIP cleaning
- High pressure, hose down cleaning flexibility
- High levels of chemical resistance
- Resistance to high temperatures and temperature shock
- AISI 316 flangeless wafer design
- High confidence validation and accuracy in batch processing applications
- Custody transfer approvals available
- Meets 3A sanitary and EHEDG requirements

Hazardous areas

For installations in hazardous areas the flowmeters are available with FM and ATEX approvals in remote or compact design. Still the full functionality is given by the touch keypad and multi lingual display.







PFA reinforced with stainless steel mask has excellent mechanical stability characteristics to ensure long term stability.







MAG 6000 I (Ex d)



MAG 5000/6000 wallmount



MAG 1100 with pipe threads



Food and Beverage A higher standard of precision and purity

Siemens provides flow solutions for the food and beverage industry to efficiently manage flow processes, giving them a competitive edge.

Our flowmeters are designed to meet the challenges in the tough environment of the food and beverage industry where extreme temperature changes, humidity, condensation, hose-down and CIP cleaning are ever present.

The sanitary solution

MAG 1100 F is specially designed for the food and beverage industry. It was the first to pass the EHEDG hygienic test and meets all sanitary standards.

MAG 1100's obstructionless performance is unaffected by the suspended solids, viscosity, and temperature challenges typically found in food and beverage processes.

Your guarantee for hygienic food safety

- AISI 316 stainless steel enclosure
- Hygienic seal, EHEDG and 3A approvals
- Suitable for CIP and SIP cleaning
- IP67 / NEMA 4X rating that is upgradeable to IP68 / NEMA 6P
- Delivered with your specified connection; with metal-to-metal design, no grounding connection is required.
- Direct access to covered keypad and display
- Accredited custody transfer approvals





EHEDG





Process connections With the unique and flexible adaptor concept, one flowmeter fits nearly every process connection. Adaptors are

connection. Adaptors are offered for clamp connection, threaded connection or weld in type connection for direct welding into the process piping.

TRANSMAG 2: Designed for all heavy-duty applications



Benefits for heavy-duty solutions

- Eliminates problems related to zero-point stability
- No movable parts that can wear or degrade measurement accuracy
- Electrode noise-resistant
- Noise-resistant
- Heavy-duty industrial enclosure
- A wide choice of corrosionresistant liner materials



Pulsed AC technology

The pulsed AC TRANSMAG 2 flowmeter generates a strong magnetic field, a high excitation frequency and a stable zero point. Providing an accurate, repeatable, fast responding and stable flow signal.

TRANSMAG 2 AC Flowmeter. A Siemens Exclusive.

Thanks to its pulsed alternating field system, the TRANSMAG 2 is capable of measuring where conventional DC field technology can not, like in applications involving:

- High concentrated pulp stock
- Heavy mining slurries
- Mining slurries with magnetic particals

The alternating field technology generates a much stronger magnetic field within the sensor compared to DC technology. This is why it measures more reliably and with greater precision – even when the media has a high concentration of solids. Thanks to its patented signal integration, the TRANSMAG 2 provides only the real flow measurement by removing unwanted electrode noise from the sensor's signal. With the pulsed AC technology, it's possible to have a stable zeropoint, thereby a reliable and accurate measurement.



Transmitter	TRANSMAG 2			
Measuring principle	Pulsed alternating field			
Enclosure	IP67 / NEMA 4X			
Max measuring Error	0,50% of rate			
Display	2 line alpha numeric LCD with back light			
Inputs & outputs	1 current, 1 digital, 1 relay (or 1 digital input) output			
Communication	HART, Profibus PA			
Power Supply	100 – 230 V AC			

Pulp & Paper and Mineral Industries Heavy duty solutions for tough applications

Pulp & Paper Industry

Siemens MAGFLO and TRANSMAG 2 flowmeters offer exceptional value for pulp & paper applications. They are well-suited for any flow applications even with high solids content and are ready to take on your toughest applications – no matter how challenging they may be!

Pulp

The high energy magnetic field generated with pulsed AC technology provides a powerful signal ideal for measuring high concentrations of paper stock, i.e., greater than 3 %.

Mining Industry

Rugged in design and unaffected by electrode noise, disturbances or vibration, Siemens MAGFLO flowmeters for the mineral industry can be easily installed virtually anywhere.

All models produce accurate and repeatable results, contributing to improved quality-based performance.

Slurries

The high energy magnetic field generated with pulsed AC technology provides a powerful signal ideal for measuring high concentrations of slurries.

Magnetic particles – no problem

Magnetic particles in the media will boost the magnetic field in the flowmeter and course a misreading. To overcome this, the TRANSMAG 2 is designed with a second compensating coil circuit.

Maximum protection

There's a solution for every abrasive media application, but the choice of material is crucial to protect the flowmeter. Besides inlet protection rings, Siemens offers a wide range of liner and electrode materials. Especially the soft LINATEX rubber and the NOVOLAK liner have proven themselves in these harsh environments.





Compensation coil

The TRANSMAG 2 offers a second coil circuit to compensate for fluctuations in the magnetic field, caused by fluctuations in the main power supply or magnetic particles in the media.



LINATEX Protection Minerals or particles will bounce off the soft rubber liner, instead of wearing it down.



TRANSMAG 2



MAG 6000 I – MAG 3100



MAG 5000/6000



MAG 1100



MAG 5100 W

Continuous Accuracy. Verifiable Confidence.



(400) (680) 🖢 DANAK 🚈 🔞

Calibration

To ensure accurate flow measurement, a flowmeter must be validated through calibration. Every Siemens flowmeter is calibrated at facilities that are individually accredited in accordance with EN 45001 EA by UKAS, DANAK and traceable to NIST. A calibration certificate is shipped with every Siemens sensor. Siemens Calibration facilities comply with ISO 9001.

- High accuracy rigs with better than 0.1% calibration uncertainty
- laboratory #0301
- Documentation for ISO 9000 and ISO 14001 management system



(РТВ)

G





Meter performance

Thanks to their reliable performance, electromagnetic flowmeters are those recommended most for measurement of conductive liquids. Siemens flowmeters, among the best in the world, comply with standards such as custody transfer approvals for billing purpose. They deliver;

- Uncertainty better than 0.25%/0.5% down to 0.5 m/s/ 1.5 ft/s
- PTB type approvals (cold water), OMIL R75 and OIML R117
- Comply with OIML R49 and ISO 4064

MAGFLO SENSORPROM

During the calibration process, measurement parameters and "Fingerprint" data, as well as other important data are stored in the SENSORPROM memory:

- · Sensor information and identification
- Calibration parameters
- Fingerprint parameters
- Default flowmeter settings



In-situ MAGFLO verification – three simple steps

Through in-depth analysis, Siemens has identified the parameters which influence the accuracy of a flowmeter operating in the real world.

These parameters are checked using a unique, patented verification technique for MAGFLO flowmeters. Testing at WRc proved the accuracy of the verification result for a complete flowmeter.

Transmitter Test

The transmitter test is a flow simulation test that checks the whole electronic system from signal input to output. Using the magnetic field energy, the Verificator simulates a flow signal to the transmitter input.

By measuring the transmitter output, the Verificator calculates its accuracy against factory defined values.

2 Flowmeter Insulation Test

The verification test of the flowmeter insulation is a "cross-talk" test of the entire flowmeter. It ensures that the sensor flow signal is unaffected by external influences.

In this test, the Verificator generates a high voltage disturbance within the coil circuit and then looks for any "cross-talk" induced in the flow signal circuit. By generating dynamic disturbances close to the



Namo Address			MAG	LOB Identif	ication:		
Address	Arta Food		TAG	io./Namo	0		
	Address Samdon		Senso		083G5074		
	Asbenras		Senso	r Serial No.	107901711	10	
	Alan Pedersen		Conve	rter Code No.	083F5001		
Phone			Conve	rter Serial No.	305414N05	50	
Email			Locati	Location		Indvojning F02	
Results:		fication file nam	ne or No.	File #16			
	Col	werter wor insulation		Passed			
	Ser	Magnetic		Passed			
				Passed			
Velocity		Current Output			Freq. 0		
Theoretical	Theoretical		Deviation	Theoretical	Actual		Deviatio
0,5m/s	4,800mA	4,802mA	0,19%	0,500kHz	0,5004		-0,05%
1,0m/s 3,0m/s	5,600mA 8,800mA	5,600mA 8,797mA	0.02%	1.000kHz 3.000kHz	0.99965		-0.08%
2,2414	Current Outp		-0,0875	Freq. Outpu			-0,0855
Converter	Rettings:			Sensor D	etaile:		
Banic .	STREET,			Size	CONTRACTOR.	-	
	2max	100.00 m ^h h		509			
Low	Now Direction	Positive		CH ENN			5.833800
	.ow-flow Cutoff (mpty Pipe	4.00%		0.00.7.00.0		-,	
Output		-		Correction	Factor	1.000	300
0	Current Output Time Constant	ON (4-20mA) 5.00 Sec.					
				Excitation		3,125	Hz
1	Relay Output	OFF			riogaciecy		
1		OFF OFF					
1	Nelay Output Digital Output Frequency Range	OFF Not Valid		Verificate			
	Relay Output Digital Output Trequency Range Time Constant	OFF Not Valid Not Valid		Verificate Serial No.			3N510
	Relay Output Sigital Output Frequency Range Fime Constant Autmo/pulso Pulse width	OFF Not Valid			r Detalls		3N510
	Relay Output Digital Output Frequency Range Fime Constant Ablumc/pulso	OFF Not Valid Not Valid 0.0 m*p		Serial No.	er Details	00230	3N510
Totalizer 1	Relay Output Digital Output Inequency Range Irime Constant Adumolpulso Pulse width Pulse polarity value before test	OFF Not Valid 0.0 m ¹ /p N/A N/A 18851918.0 I		Serial No. Hardware Software	er Details	00230	3N510
Totalizer 1 Totalizer 1	Relay Output Digital Output Inequency Range Time Constant Adumo/pulso Pulse width Pulse polarity	OFF Not Valid 0.0 m ¹ /p N/A N/A		Serial No. Hardware Software	version	00230 1.00 1.26	

flow signal the flowmeter is tested for noise immunity to a maximum level.

Sensor Magnetism Test

The verification of the sensor magnetism is a "boost" test of the magnetic field coil. It ensures that the magnetism behaviour compares to its original behavior by comparing the current sensor magnetism with the "fingerprint" determined during initial calibration and stored in the SENSORPROM.

In the "Boost" test the Verificator changes the magnetic field pattern and uses high voltage to get quick stable magnetic condition.

Certificate

An authorized, signed certificate documents the verification and includes:

- Test result with pass or failed approval
- Installation specification
- Flowmeter specification and configuration
- Verificator specification with date of calibration ensuring traceability to national and international standards.



Flow Simulation Test



"Cross-Talk" Test



"Boost" Test



What independent testing by WRc says: **"The MAGFLO Verificator correctly detected** all set-up faults in the complete flowmeter...is **straightforward** to use.....is **sturdy and suitable** for field use"

WRc, Water Research Centre is a leading, independent research, technology and consultancy company with a reputation for scientific and technical excellence. WRc has over 15 years of experience in instrument testing and evaluation. WRc's full report, UC3600 March 2000, is available for inspection.

To locate your Siemens partners worldwide...

... contact us at our homepage www.siemens.com/processinstrumentation www.siemens.com/flow and look under "Contact"







Siemens Flow Instruments A/S DK-6430 Nordborg Denmark

www.siemens.com/processautomation

SITRANS, MAGFLO, SENSORPROM and TRANSMAG 2 are registered trademarks of Siemens. Other designations used in this publication may be trademarks whose use by third parties for their own purposes can violate the rights of the owners.

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.